

**BD FACSCanto configuration:**

Lasers	PMT	Dichroic mirror	BP filter	Fluorochromes option
Blue 488 nm	A	735LP	780/60	PE-Cy7, PE-Alexa750
	B	655LP	670/LP	PerCP, PerCP-Cy5.5, PE-Cy5, PE-Cy5.5, 7-AAD, PerCP-eFluor710, PE-Alexa700, PE-Alexa647
	C	556LP	585/42	PE, DsRed, PI*
	D	502LP	530/30	FITC, GFP, CFSE, Alexa488, DiOC6, eYFP, Alexa430
	E	NONE	488/10	SSC
	F	N/A	N/A	No PMT
	G	N/A	N/A	No PMT
Red 633 nm	A	735LP	780/60	APC-CY7, APC-H7, APC-Alexa750, Alexa750, APC-eFluor780
	B	VIDE	660/20	APC, Alexa647, Alexa633, Cy5, eFluor660, To-Pro3
	C	N/A	N/A	No PMT